

Technical data sheet

Ceramic terminal

Item number: 7205700



High-temperature-resistant ceramic terminal for refitting of the FireBox T series.
Tested according to DIN EN 60998-2-1:2004.



E30

E60

E90

Steatit

Master data	
Item number	7205700
Type	TK 04
Description 1	Ceramic terminal w. wire prot.
Description 2	for FireBox T data technology
Manufacturer	OBO
Dimension	4 mm²
Colour	Cream
Material	Steatit
Smallest sales unit	5
Unit of quantity	Piece
Weight	0.88 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0029 kg COe / 1 Piece


Technical data sheet

Ceramic terminal

Item number: 7205700



Dimensions



Length	8.5 mm
Width	21.5 mm
Height	21.5 mm

Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, min.	4 mm ²
Connection position	Side
No. of terminals	2
Number of screwless terminals per pole	2
Version of electrical connection 1	Screw connection
Version of electrical connection 2	Screw connection
Explosion-tested version	no
Insulation material	Ceramic
Mounting type	Miscellaneous
Nominal cross-section, max.	4 mm ²
Nominal cross-section, min.	0.5 mm ²
Nominal voltage	400 V
Nominal current	32 A
Pole number	1
Permitted temperature range, min.	250 °C
Transparent	no