Technical data sheet

Junction box T100, closed, elevated cover

Item number: 2007732





Closed junction box for the connection of cables in indoor and protected outdoor areas. Rectangular design without entries. Suitable for wall and ceiling mounting and on mounting panels. With the option of fastening inside and to mount via the corner domes. High cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

With hat profile rail.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650°C. Impact resistance IK07 according to DIN EN 50102. Clear internal dimensions: 136x102x74 mm



Master data

| Item number | 2007732 |
|----------------------------------------|-------------------------------|
| Туре | T 100 OE HD LGR |
| Description 1 | Junction box, closed |
| Description 2 | with raised cover |
| Manufacturer | OBO |
| Dimension | 150x116x83 |
| Colour | Light grey; RAL 7035 |
| Material | Polypropylene / polycarbonate |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 23.65 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to- Gate | 1,0622 kg COe / 1 Piece |

Technical data sheet

Junction box T100, closed, elevated cover

Item number: 2007732



Length 150 mm Width 116 mm Height 83 mm



Technical data

| Expandable | yes |
|-----------------------------------|-----------------------------------------------------------|
| Type of insertion | None |
| Type of entry | Cable |
| Type of housing penetration | Without |
| Measured insulation voltage Vi | 500 V |
| Equipment | Without |
| Cover | Not transparent |
| Cover fastening | Screwed |
| Entry from rear | yes |
| Entries | None |
| Explosion-tested version | no |
| Flame-resistant | acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C |
| Shape | Rectangular |
| Maintain electrical functions | Without |
| For Ex zone | Without |
| For Ex zone gas | Without |
| For Ex zone dust | Without |
| Halogen-free | yes |
| Clear internal dimensions | 136x102x74 mm |
| With screening | no |
| with lid | yes |
| Mounting type | Wall/ceiling mounting |
| Nominal voltage | 500 V |
| Sealable | yes |
| Protection rating | IP66 |
| Protection rating IK code | IK07. |
| Permitted temperature range, max. | 60 °C |

Technical data sheet

Junction box T100, closed, elevated cover

Item number: 2007732

Technical data

| Permitted temperature range, min. | -5 °C |
|-----------------------------------|-------|
| Weatherproof | no |