Technical data sheet

Junction box T 160, plug-in seal, terminal strip

Item number: 2007440





Junction box with terminal strip for the connection of cables and lines indoors and in protected outdoor areas. Rectangular design with plug-in seals to the sides and knock-out entries in the bottom. Suitable for wall and ceiling mounting and on mounting panels. With the option to fasten inside and to mount via the corner domes. Cover with quick lock, sealable. Made from halogen-free and UVresistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK05 according to DIN EN 50102. Terminal strips and mounting rail are not pre-installed





Polypropylene, fibreglass reinforced

Master data

Item number	2007440
Туре	T 160 KL
Description 1	Junction box
Description 2	with terminal strip + entries
Manufacturer	OBO
Dimension	190x150x77
Colour	Light grey; RAL 7035
Material	Polypropylene, fibreglass reinforced
Smallest sales unit	1
Unit of quantity	Piece
Weight	43.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to- Gate	1,8828 kg COe / 1 Piece

Technical data sheet

Junction box T 160, plug-in seal, terminal strip

Item number: 2007440



Dimensions Image: State of the state of the

Technical data

190

Expandable	yes
No. of entries	12
Number of terminals	5
Type of insertion	Plug-in seal
Type of entry	Cable
Type of housing penetration	Cuttable stepped membrane
Measured insulation voltage Vi	500 V
Equipment	Terminal
Cover	Not transparent
Cover fastening	Screwed
Entry from rear	yes
Entries	7 x M25
	5 x M32
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Rectangular
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Fibre-glass reinforced	yes
Halogen-free	yes
Clear internal dimensions	176x135x67 mm
With screening	no
with lid	yes
Mounting type	Wall/ceiling mounting
Nominal cross-section, min.	16 mm ²
Nominal voltage	500 V
Sealable	yes
Protection rating	IP66
Protection rating IK code	IK05.
Permitted temperature range, max.	60 °C

Technical data sheet

Junction box T 160, plug-in seal, terminal strip

Item number: 2007440



Technical data

Permitted temperature range, min.	-5 °C
Transparent lid	no
Weatherproof	no