# **Technical data sheet**

# **UP Flush-mounted device connection box 66**

**Item number: 2003702** 





Flush-mounted device box, for use in masonry with an installation depth of at least 66 mm.

- 4 x 3 screw domes
- Connection nozzle with bayonet lock, couplable on both sides
  6 combination pipe entries up to Ø 20 and 25 mm
  4 entries up to Ø 20 mm

- 2 entries up to Ø 14 mm

• 1 entry up to Ø 20 mm in the base Tested according to DIN EN 60670-1, DIN EN 60670-22 and DIN 49073-1.

















Polypropylene

#### Master data

2003702
UG 66
UP Flush-mounted device box
01.10.2021
OBO
Ø60mm, H66mm
Jet black
Polypropylene
25
Piece
2.39 kg
kg/100 pc.
0,0892 kg COe / 1 Piece

# **Technical data sheet**

### **UP Flush-mounted device connection box 66**



**Item number: 2003702** 



### Technical data

Ø 61

No. of entries	13
Type of insertion	NYM cables, data cables and corrugated pipes
Type of housing penetration	Break-out opening
Version for	Single
Type	Device connection box
Device fixing	Screws or spreading claws
Cover	Without
Cover fastening	Screws,
Entry from rear	yes
Entries	11
Flame-resistant	acc. to VDE 0471/IEC 60695-2-11, test temperature 650°C
Shape	Round
for pipe diameter	20/25 mm
Halogen-free	yes
Combination entries Ø 20 / 25 mm	6
With nail strap	no
With bolts	no
Mounting type	Concealed
Nominal cross-section, max.	2.5 mm²
Nominal cross-section, min.	1.5 mm²
Pipe entries Ø 20 mm	3
Impact-resistant	yes
Protection rating	IP30
Airtight	no
Rated voltage	400 V