

Technical data sheet

UVS-WIN energy distributor with fixed connection, special circuit

Item number: 6107982



Energy distributor for heavy current technology with fixed connection, equipped and pre-wired.

Input: 1x three-phase circuit via a screwless terminal block, 5-pin, for cable cross-sections of 0.5–4 mm².

Output: 6 self-locking plug connectors, 3-pin, in white, 25 A, type WINSTA (socket part 2x L1, 2x L2, 2 x L3)

Internal wiring: H07V-U2.5

Input: 1x rotary current circuit via a screwless terminal block, 5-pin, for cable cross-sections of 0.5–4 mm².

Output: 6 self-locking plug connectors, 3-pin, in white, 25 A, type WINSTA® MIDI (socket part: 2x L1, 2x L2, 2x L3).

Internal wiring: PVC non-sheathed cable H07V-U2.5.

St Steel

Master data

Item number	6107982
Type	UVS-WIN F6W
Description 1	Underfloor distributor
Description 2	Fixed connection, 6 WINSTA
Manufacturer	OBO
Dimension	150x196x46
Material	Steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	76.3 kg
Weight unit	kg/100 pc.


Technical data sheet

UVS-WIN energy distributor with fixed connection, special circuit

Item number: 6107982



Dimensions



Length	196 mm
Width	149 mm
Height	46 mm

Technical data

Connection type	Terminal block
No. of outlets	6
Number of input circuits	1
Input	5-pole
Colour of the plug connector system	White
Suitable for through wiring	no
Cross-section of the connection cable	4 mm ²
Plug connector system, system-specific	yes