

Technical data sheet

Cable gland, metric thread, light grey

Item number: 2022362



Cable gland with metric connection thread in cap nut design, suitable for junction boxes, housings, distributor cabinets in private and industrial areas. With strain relief and integrated sealing lip, tested according to DIN EN 62444. Protection class IP68. Can be used between -20°C and +65°C. Table column D: sealing range to VDE 0619, in which no strain relief is required. Table column D2: sealing range including strain relief and twist protection to VDE 0619



PA Polyamide

Master data

Item number	2022362
Type	V-TEC M25 LGR
Description 1	Cable gland
Description 2	metric
Manufacturer	OBO
Dimension	M25
Colour	Light grey; RAL 7035
Material	Polyamide
Smallest sales unit	25
Unit of quantity	Piece
Weight	2.35 kg
Weight unit	kg/100 pc.


Technical data sheet

Cable gland, metric thread, light grey

Item number: 2022362



Dimensions



Dimension L max.	38 mm
Dimension L min.	28 mm
Dimension L1	11 mm
Dimension L2	6 mm
Dimension L3	22 mm
Dimension L4	12.5 mm

Technical data sheet

Cable gland, metric thread, light grey

Item number: 2022362



Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
Sealing area D, max.	18 mm
Sealing area D, min.	9 mm
explosion-proof	no
Flat cable gland	no
For Ex zone	Without
Thread	M25 x 1,5
Thread type	Metric
Fibre-glass reinforced	no
Halogen-free	yes
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF	33
Protection rating	IP68
Permitted temperature range, max.	65 °C
Permitted temperature range, min.	-20 °C
Strain relief and wringing protection D2, max.	18 mm
Strain relief and wringing protection D2, min.	12 mm
Strain relief option	yes