

Technical data sheet

Injection mortar in cartridge, 420 ml

Item number: 3497803



Styrene-free, vinyl ester composite mortar for spread-free anchoring of high loads with threaded anchor rods. Coaxial cartridge, including one mixing tube, to be worked with the pressing gun, type VM-P 380 Profi.

European Technical Assessment for cracked and uncracked concrete, as well as for masonry of full and hollow brick. Earthquake-proof in concrete according to Category C1. Fire protection approval for concrete and masonry with fire resistance classes up to 120 minutes.

Substrate temperature during processing -10°C to $+40^{\circ}\text{C}$ (concrete), ambient temperature after complete hardening -40°C to $+120^{\circ}\text{C}$ (in concrete). If stored in a dark, cool and dry place, will keep for at least 18 months.

Special mortar

Master data

Item number	3497803
Description 1	Injection mortar
Description 2	in cartridge
Manufacturer	OBO
Dimension	420ml
Colour	Grey
Material	Special mortar
Smallest sales unit	1
Unit of quantity	Piece
Weight	83 kg
Weight unit	kg/100 pc.

Technical data

Adhesive application	Construction/mounting
Hardening method	2-component
Contents	420 ml
Delivery form	Cartridge
With brush	no
Transparent	no