


Technical data sheet

Cover for 90° bend DD

Item number: 6231535



Cover for wide span 90° bend with pre-mounted turn buckles.
As the connector is mounted from the outside, the fitting cover is 300 mm shorter than the corresponding fitting. This must be considered when installing the track elements.




St Steel

DD Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6231535
Description 1	90° bend cover
Description 2	wide span system 110 and 160
Manufacturer	OBO
Dimension	B300mm
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	270 kg
Weight unit	kg/100 pc.

Dimensions



Width	300 mm
Height	110 mm
Plate thickness	1 mm
Dimension B	300 mm
Dimension H	15 mm

Technical data sheet

Cover for 90° bend DD

Item number: 6231535



Technical data

Bend (angle)	90°
Number of turn buckles	7 St.
Fastening type	Sash lock
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Rustproof steel, pickled	no
Hinged	no