


# Technical data sheet

## Cover for 90° bend FS

Item number: 6231489



Cover for wide span 90° bend with pre-mounted turn buckles.  
As the connector is mounted from the outside, the fitting cover is 300 mm shorter than the corresponding fitting. This must be considered when installing the track elements.




St	Steel
FS	Strip galvanized

### Master data

Item number	6231489
Type	WDBRL 90 40 FS
Description 1	90° bend cover
Description 2	wide span system 110 and 160
Manufacturer	OBO
Dimension	B400mm
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	449 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	20,8123 kg CO2e / 1 Piece

### Dimensions



Width	400 mm
Height	110 mm
Plate thickness	1 mm
Dimension B	400 mm
Dimension H	15 mm

# Technical data sheet

Cover for 90° bend FS

Item number: 6231489



## Technical data

Bend (angle)	90°
Number of turn buckles	7 St.
Fastening type	Sash lock
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Rustproof steel, pickled	no