


Technical data sheet

Trunking, type WDK 40060

Item number: 6025633



Trunking cover and base with base perforation.
Four cover fixing devices included.
Lid clamp can be moved along the entire length of the trunking.



PVC Polyvinylchloride

Master data	
Item number	6025633
Description 1	Wall trunking system
Description 2	with base perforation
Manufacturer	OBO
Dimension	40x60x2000
Colour	Stone grey; RAL 7030
Material	Polyvinylchloride
Smallest sales unit	32
Unit of quantity	Metre
Weight	56.2 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	0,9691 kg COe / 1 Meter

Technical data sheet


Trunking, type WDK 40060

Item number: 6025633



Dimensions

Length	2,000 mm
Width	60 mm
Height	40 mm



Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm ² Ø 10.5 mm (without socket)	10
Number of cables NYM 3 x 2.5 mm ² Ø 11.5 mm (without socket)	8
Number of cables NYM 5 x 1.5 mm ² Ø 12.0 mm (without socket)	7
Number of insertable partitions	1
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	yes
Duct connector	yes
Delivery on a roll	no
Usable cross-section	1775 mm ²
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C