

Technical data sheet

Trunking, type WDK 40060

Item number: 6027024



Trunking cover and base with base perforation.
Four cover fixing devices included.
Lid clamp can be moved along the entire length of the trunking.



PVC Polyvinylchloride

Master data		
Item number	6027024	
Description 1	Wall trunking system	
Description 2	with base perforation	
Manufacturer	OBO	
Dimension	40x60x2000	
Colour	Light grey; RAL 7035	
Material	Polyvinylchloride	
Smallest sales unit	32	
Unit of quantity	Metre	
Weight	56.2 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	0,9603 kg COe / 1 Meter	

Technical data sheet


Trunking, type WDK 40060

Item number: 6027024



Dimensions

Length	2,000 mm
Width	60 mm
Height	40 mm



Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm ² Ø 10.5 mm (without socket)	10
Number of cables NYM 3 x 2.5 mm ² Ø 11.5 mm (without socket)	8
Number of cables NYM 5 x 1.5 mm ² Ø 12.0 mm (without socket)	7
Number of insertable partitions	1
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	yes
Duct connector	no
Delivery on a roll	no
Usable cross-section	1775 mm ²
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C