

Technical data sheet

External corner cover, trunking type WDK 60210

Item number: 6182666



External corner hood for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data		
Item number	6182666	
Type	WDK HA60210LGR	
Description 1	External corner hood	
Manufacturer	OBO	
Dimension	60x210mm	
Colour	Light grey; RAL 7035	
Material	Polyvinylchloride	
Smallest sales unit	2	
Unit of quantity	Piece	
Weight	20.357 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,4229 kg CO2e / 1 Piece	

Technical data sheet

External corner cover, trunking type WDK 60210

Item number: 6182666



Dimensions



Length	100 mm
Width	210 mm
Height	60 mm
Dimension a	100 mm
Dimension H	210 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	60 x 210
Halogen-free	no
Trunking depth	60 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Self-extinguishing	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm