

Technical data sheet

End piece, trunking type WDK 15040

Item number: 6193110



End piece to close the WDK trunking.
The end pieces are pushed onto the WDK trunking and are fixed on the connector by spring force.



PVC Polyvinylchloride

Master data

Item number	6193110
Description 1	End piece
Manufacturer	OBO
Dimension	15x40mm
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.299 kg
Weight unit	kg/100 pc.

Technical data sheet

End piece, trunking type WDK 15040

Item number: 6193110



Dimensions



Length	17 mm
Width	40 mm
Height	17 mm
Dimension a	40 mm
Dimension b	17 mm
Dimension H	40 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C