

Technical data sheet

End piece, trunking type WDK 20020

Item number: 6158706



End piece to close the WDK trunking.

The end pieces are pushed onto the WDK trunking and are fixed on the floor connector by spring force.




PVC Polyvinylchloride

Master data

Item number	6158706
Description 1	End piece
Manufacturer	OBO
Dimension	20x20mm
Colour	Stone grey; RAL 7030
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.101 kg
Weight unit	kg/100 pc.

Dimensions



Length	11.5 mm
Width	17 mm
Height	17 mm
Dimension a	17 mm
Dimension b	17 mm
Dimension H	20 mm

Technical data sheet

End piece, trunking type WDK 20020

Item number: 6158706



Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C