

Technical data sheet

End piece, trunking type WDK 60110

Item number: 6191812



End piece for closing the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



PVC Polyvinylchloride

Master data

Item number	6191812
Type	WDK HE60110SW
Description 1	End piece
Manufacturer	OBO
Dimension	60x110
Colour	Jet black; RAL 9005
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	2.937 kg
Weight unit	kg/100 pc.

Dimensions

Length	27.5 mm
Width	110 mm
Height	60 mm
Dimension a	110 mm
Dimension b	60 mm
Dimension H	110 mm

Technical data sheet

End piece, trunking type WDK 60110

Item number: 6191812



Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protective film	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C