

Technical data sheet

End piece, trunking type WDK 60150

Item number: 6193323



End piece to close the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



PVC Polyvinylchloride

Master data		
Item number	6193323	
Description 1	End piece	
Manufacturer	OBO	
Dimension	60x150mm	
Colour	Pure white; RAL 9010	
Material	Polyvinylchloride	
Smallest sales unit	10	
Unit of quantity	Piece	
Weight	4.118 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	13,8426 kg COe / 1 Piece	

Technical data sheet

End piece, trunking type WDK 60150

Item number: 6193323



Dimensions



Length	27.5 mm
Width	150 mm
Height	60 mm
Dimension a	150 mm
Dimension b	60 mm
Dimension H	150 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C