

Technical data sheet

End piece, trunking type WDK 60150

Item number: 6193462



End piece to close the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



PVC Polyvinylchloride

Master data

Item number	6193462
Type	WDK HE60150VW
Description 1	End piece
Manufacturer	OBO
Dimension	60x150mm
Colour	Traffic white; RAL 9016
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	4.118 kg
Weight unit	kg/100 pc.


Technical data sheet

End piece, trunking type WDK 60150

Item number: 6193462



Dimensions



Length	27.5 mm
Width	150 mm
Height	60 mm
Dimension a	150 mm
Dimension b	60 mm
Dimension H	150 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C