

Technical data sheet

End piece, trunking type WDK 60230

Item number: 6183875



End piece to close the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



PVC

 Polyvinylchloride

Master data	
Item number	6183875
Description 1	End piece
Manufacturer	OBO
Dimension	60x230mm
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	6.283 kg
Weight unit	kg/100 pc.

Technical data sheet

End piece, trunking type WDK 60230

Item number: 6183875



Dimensions



Length	27.5 mm
Width	230 mm
Height	60 mm
Dimension a	230 mm
Dimension b	60 mm
Dimension H	230 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C