

Technical data sheet

Flat angle cover, trunking type WDK 15030

Item number: 6192750



Flat angle hood for changing the direction of the WDK trunking.



PVC

 Polyvinylchloride

Master data	
Item number	6192750
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	15x30mm
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	4
Unit of quantity	Piece
Weight	0.965 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0381 kg COe / 1 Piece

Technical data sheet

Flat angle cover, trunking type WDK 15030

Item number: 6192750



Dimensions



Length	53 mm
Width	30 mm
Height	17.5 mm
Dimension a	53 mm
Dimension H	30 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	15 x 30
Halogen-free	no
Trunking depth	15 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm