

# Technical data sheet

Flat angle cover, for trunking type WDK 15040

Item number: 6161227



Flat angle hood for changing the direction of the WDK trunking.



**PVC** Polyvinylchloride

| Master data         |                   |
|---------------------|-------------------|
| Item number         | 6161227           |
| Description 1       | Flat angle cover  |
| Manufacturer        | OBO               |
| Dimension           | 15x40mm           |
| Colour              | Cream; RAL 9001   |
| Material            | Polyvinylchloride |
| Smallest sales unit | 4                 |
| Unit of quantity    | Piece             |
| Weight              | 1.5 kg            |
| Weight unit         | kg/100 pc.        |

# Technical data sheet

Flat angle cover, for trunking type WDK 15040

Item number: 6161227



## Dimensions



|             |       |
|-------------|-------|
| Length      | 63 mm |
| Width       | 40 mm |
| Height      | 15 mm |
| Dimension a | 63 mm |
| Dimension H | 40 mm |

## Technical data

|                                   |              |
|-----------------------------------|--------------|
| Version for                       | Hood fitting |
| Fastening type                    | Lockable     |
| Maintain electrical functions     | no           |
| for duct dimension                | 15 x 40      |
| Halogen-free                      | no           |
| Trunking depth                    | 15 mm        |
| Protection rating                 | IP30         |
| Protective film                   | no           |
| Protection rating IK code         | IK04         |
| Permitted temperature range, max. | 60 °C        |
| Permitted temperature range, min. | -5 °C        |
| Angle range, max.                 | 90 mm        |
| Angle range, min.                 | 90 mm        |