

Technical data sheet

Flat angle cover, trunking type WDK 20020

Item number: 6183212



Flat angle cover for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data

Item number	6183212
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	20x20mm
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	4
Unit of quantity	Piece
Weight	0.596 kg
Weight unit	kg/100 pc.

Technical data sheet

Flat angle cover, trunking type WDK 20020

Item number: 6183212



Dimensions



Length	38 mm
Width	20 mm
Height	17.5 mm
Dimension a	38 mm
Dimension H	20 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	20 x 20
Halogen-free	no
Trunking depth	20 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm