

Technical data sheet

Flat angle cover, trunking type WDK 30045

Item number: 6183301



Flat angle hood for changing the direction of the WDK trunking.



PVC

 Polyvinylchloride

Master data		
Item number	6183301	
Type	WDK HF30045LGR	
Description 1	Flat angle cover	
Manufacturer	OBO	
Dimension	30x45mm	
Colour	Light grey; RAL 7035	
Material	Polyvinylchloride	
Smallest sales unit	4	
Unit of quantity	Piece	
Weight	1.922 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,0565 kg CO2e / 1 Piece	

Technical data sheet

Flat angle cover, trunking type WDK 30045

Item number: 6183301



Dimensions



Length	68 mm
Width	45 mm
Height	30 mm
Dimension a	68 mm
Dimension H	45 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	30 x 45
Halogen-free	no
Trunking depth	30 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm