

Technical data sheet

Flat angle cover, trunking type WDK 40060

Item number: 6161308



Flat angle hood for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data

Item number	6161308
Type	WDK HF40060CW
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	40x60mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Piece
Weight	6.271 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2287 kg CO2e / 1 Piece


Technical data sheet

Flat angle cover, trunking type WDK 40060

Item number: 6161308



Dimensions



Length	101 mm
Width	65 mm
Height	40 mm
Dimension a	101 mm
Dimension H	60 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	40 x 60
Halogen-free	no
Trunking depth	40 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm