

Technical data sheet

Flat angle cover, trunking type WDK 60090

Item number: 6161510



Flat angle hood for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data

Item number	6161510
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	60x90mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Piece
Weight	11.454 kg
Weight unit	kg/100 pc.


Technical data sheet

Flat angle cover, trunking type WDK 60090

Item number: 6161510



Dimensions



Length	129 mm
Width	94 mm
Height	60 mm
Dimension a	129 mm
Dimension H	90 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	60 x 90
Halogen-free	no
Trunking depth	60 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm