

# Technical data sheet

## Flat angle cover, trunking type WDK 60210

Item number: 6183476



Flat angle hood for changing the direction of the WDK trunking.



**PVC** Polyvinylchloride

### Master data

|                     |                      |
|---------------------|----------------------|
| Item number         | 6183476              |
| Description 1       | Flat angle cover     |
| Manufacturer        | OBO                  |
| Dimension           | 60x210mm             |
| Colour              | Light grey; RAL 7035 |
| Material            | Polyvinylchloride    |
| Smallest sales unit | 2                    |
| Unit of quantity    | Piece                |
| Weight              | 38 kg                |
| Weight unit         | kg/100 pc.           |

# Technical data sheet

## Flat angle cover, trunking type WDK 60210

Item number: 6183476



### Dimensions



|             |        |
|-------------|--------|
| Length      | 250 mm |
| Width       | 210 mm |
| Height      | 60 mm  |
| Dimension a | 250 mm |
| Dimension H | 210 mm |

### Technical data

|                                   |              |
|-----------------------------------|--------------|
| Version for                       | Hood fitting |
| Fastening type                    | Lockable     |
| Maintain electrical functions     | no           |
| for duct dimension                | 60 x 210     |
| Halogen-free                      | no           |
| Trunking depth                    | 60 mm        |
| Protection rating                 | IP30         |
| Protective film                   | no           |
| Protection rating IK code         | IK04         |
| Permitted temperature range, max. | 60 °C        |
| Permitted temperature range, min. | -5 °C        |
| Angle range, max.                 | 90 mm        |
| Angle range, min.                 | 90 mm        |