

Technical data sheet

90° vertical bend, rising, 160 FT

Item number: 6230431



90° vertical bend, for all wide span cable ladders of 160 mm side height.
For further stabilisation, additional supports should be planned for the area of the fittings.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6230431
Description 1	90° bend rising
Description 2	for wide span cable ladder 160
Manufacturer	OBO
Dimension	160x300
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	1335 kg
Weight unit	kg/100 pc.


Technical data sheet

90° vertical bend, rising, 160 FT

Item number: 6230431



Dimensions



Width	300 mm
Height	160 mm
Dimension B	300 mm
Dimension R	300 mm

Technical data

Bend (angle)	90°
Version of the rungs	Profile unperforated
Side rail version	Flat profile
Maintain electrical functions	no
Change of direction	Vertical rising
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	yes
Rail thickness	2 mm