

Technical data sheet

Large washer, A2

Item number: 3403175



Washer of particularly large outer diameter. In the case of connections on the MS 41 mounting rail, we recommend the external diameter of 40 mm.



A2 Stainless steel

2B Bright, treated

Master data

Item number	3403175
Type	WS M10 D40 A2
Description 1	Fender plate
Manufacturer	OBO
Dimension	M10, Ø40mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.592 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0293 kg COe / 1 Piece

Dimensions




Plate thickness	0.06 in
Dimension D	1.58 in
Dimension d	0.41 in
Dimension d	10.5 mm
Dimension d max.	40 mm
Dimension d min.	40 mm
Dimension h	1.5 mm

Technical data sheet

Large washer, A2

Item number: 3403175



Technical data

Thread	M10
Halogen-free	no
Material thickness	1.5 mm