

# Technical data sheet

## Empty housing X 02

Item number: 2005594



Junction box for the connection of cables and lines indoors and in outdoor areas. Square design without entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to EN 60670. Impact resistance IK09 according to EN 50102. Protection rating IP67 according to EN 60529.



**PC** Polycarbonate

Master data		
Item number	2005594	
Type	X02C SW	
Description 1	Empty Enclosure	
Manufacturer	OBO	
Dimension	95x95x72	
Colour	Graphite black; RAL 9011	
Material	Polycarbonate	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	17.5 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,7382 kg COe / 1 Piece	


# Technical data sheet

## Empty housing X 02


Item number: 2005594



### Dimensions



Length	95 mm
Width	95 mm
Height	72 mm



### Technical data

Cover fastening	Screwed
Shape	Square
Suitable for outdoor use	yes
Clear internal dimensions	85x85x57 mm
with lid	yes
Mounting type	Surface-mounted
Protection rating	IP67
Protection rating IK code	IK09
Protection class	II
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Weatherproof	yes