

Technical data sheet

Empty housing X 06

Item number: 2005602



Junction box for the connection of cables and lines indoors and in outdoor areas. Rectangular design without entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Impact resistance IK09 according to DIN EN 50102. Protection rating IP67 according to DIN EN 60529.



PC Polycarbonate

Master data

Item number	2005602
Type	X06C SW
Description 1	Empty Enclosure
Manufacturer	OBO
Dimension	150x116x86
Colour	Graphite black; RAL 9011
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	33.5 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	1,3201 kg COe / 1 Piece


Technical data sheet

Empty housing X 06


Item number: 2005602



Dimensions



Length	151 mm
Width	117 mm
Height	86 mm



Technical data

Extension option	no
Cover fastening	Screwed
Shape	Rectangular
Suitable for outdoor use	yes
Clear internal dimensions	137x105x68 mm
with lid	yes
Mounting type	Surface-mounted
Protection rating	IP67
Protection rating IK code	IK09
Protection class	II
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Weatherproof	yes