

Technical data sheet

Junction box X 06

Item number: 2005122



Junction box for the connection of cables and lines indoors and in outdoor areas. Rectangular design with knock-out entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK09 according to DIN EN 50102. Protection rating IP67 according to DIN EN 60529.



PC Polycarbonate

Master data

| | |
|-----------------------------------|--------------------------|
| Item number | 2005122 |
| Type | X06 SW |
| Description 1 | Junction box |
| Manufacturer | OBO |
| Dimension | 150x116x86 |
| Colour | Graphite black; RAL 9011 |
| Material | Polycarbonate |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 33.5 kg |
| Weight unit | kg/100 pc. |
| CO Footprint (GWP) Cradle-to-Gate | 1,3195 kg COe / 1 Piece |


Technical data sheet

Junction box X 06


Item number: 2005122



Dimensions



| | |
|--------|--------|
| Length | 151 mm |
| Width | 117 mm |
| Height | 86 mm |



Technical data

| | |
|-----------------------------------|---|
| Expandable | yes |
| No. of entries | 8 |
| Type of entry | Cuttable stepped membrane |
| Type of housing penetration | Pre-marking |
| Measured insulation voltage V_i | 750 V |
| Cover | Not transparent |
| Cover fastening | Screwed |
| Entry from rear | no |
| Entries | 4 x Ø20/25, 4 x Ø20/25/32 |
| Explosion-tested version | no |
| Flame-resistant | acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C |
| Shape | Rectangular |
| Fibre-glass reinforced | yes |
| Halogen-free | yes |
| Clear internal dimensions | 137x105x68 mm |
| Max. Conductor cross-section | 6 mm ² |
| With screening | no |
| with lid | yes |
| Mounting type | Wall/ceiling mounting |
| Nominal cross-section, max. | 6 mm ² |
| Nominal cross-section, min. | 2.5 mm ² |
| Nominal voltage | 750 V |
| Sealable | yes |
| Impact-resistant | yes |
| Protection rating | IP67 |
| Protection rating IK code | IK09 |
| Permitted temperature range, max. | 60 °C |

Technical data sheet

Junction box X 06

Item number: 2005122



Technical data

| | |
|-----------------------------------|-------|
| Permitted temperature range, min. | -5 °C |
| Transparent lid | no |
| Weatherproof | yes |