## Technical data sheet Junction box X 16 with terminal strip

#### Item number: 2005210





Junction box with terminal strip for the connection of cables and lines indoors and in outdoor areas. Rectangular design with knock-out entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials. With terminal.

With 5 terminal strips of 4 terminals each.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK09 according to DIN EN 50102. Protection rating IP67 according to DIN EN 60529. The scope of delivery contains 5 terminal strips, each with 4 terminals.



#### Master data

	Item number	2005210
	Туре	X16 T LGR
	Description 1	Junction box
	Description 2	with terminal strip
	Manufacturer	OBO
	Dimension	240x191x125
	Colour	Light grey; RAL 7035
	Material	Polycarbonate
	Smallest sales unit	1
	Unit of quantity	Piece
	Weight	97.5 kg
	Weight unit	kg/100 pc.
	CO2 Footprint (GWP) Cradle-to- Gate	3,6174 kg COe / 1 Piece

# Technical data sheet

Junction box X 16 with terminal strip

### Item number: 2005210





#### **Technical data**

Evenendeble	1400
Expandable	yes
No. of entries	10
Type of entry	Cuttable stepped membrane
Type of housing penetration	Pre-marking
Measured insulation voltage Vi	750 V
Equipment	Terminal
Cover	Not transparent
Cover fastening	Screwed
Entry from rear	no
Entries	10 x Ø25/32/40
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Rectangular
Fibre-glass reinforced	yes
Halogen-free	yes
Clear internal dimensions	227x177x110 mm
Max. Conductor cross-section	16 mm <sup>2</sup>
With screening	no
with lid	yes
Mounting type	Wall/ceiling mounting
Nominal cross-section, max.	16 mm <sup>2</sup>
Nominal cross-section, min.	6 mm²
Nominal voltage	750 V
Sealable	yes
Impact-resistant	yes
Protection rating	IP67
Protection rating IK code	IK09
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Transparent lid	no

### **Technical data sheet**

Junction box X 16 with terminal strip

Item number: 2005210



**Technical data** 

Weatherproof

yes