

Technical data sheet

isCon® conductor, Professional plus black

Item number: 5408002



Please refer to the mounting instructions for information on routing the OBO is-Con® conductor.

- Highly voltage-resistant, insulated conductor
- Floating discharge-free
- Additional mechanical protection (black protective jacket)
- For maintenance of the separation distance according to IEC 62305 (VDE 0185-305-3)
- Tested according to IEC/EN 62561-1 (VDE 0185-561-1) with H1/150 kA
- Equivalent separation distance $se \leq 0.75$ m (air) and $se \leq 1.5$ (solid material)
- Tested according to IEC TS 62561-8 (VDE V 0185-561-8)
- Halogen-free
- Fire load 4.3 kWh/m
- Can be used in potentially explosive areas Ex zone 1/2 and 21/22 when taking the current mounting instructions into account




Master data

Item number	5408002
Description 1	Insulated down conductor
Description 2	25 m roll
Manufacturer	OBO
Dimension	Ø23mm
Colour	Black
Smallest sales unit	25
Unit of quantity	Metre
Weight	69.4 kg
Weight unit	kg/100 m

Technical data sheet

isCon® conductor, Professional plus black

Item number: 5408002



Technical data

Number of individual wires	7
High voltage-resistant, insulated version	yes
Nomal ring (approx. m)	25
Length tolerance ±	5 %
Cross-section	35 mm²
Material property	Miscellaneous
Material jacket	EVA
Equivalent separating distance s(e)/m (in air)	0.75