

Technical data sheet

Fastening clip 605, medium duty, G

Item number: 1018396



St Steel

G Electrogalvanised

Two lobe fastening clips for cables and pipes.

* Sizes 7 to 12 not suitable for bolt-firing tool.

Master data

Item number	1018396
Type	605 40 G
Description 1	Fastening clip
Description 2	two lobe
Manufacturer	OBO
Dimension	40mm
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,054 kg CO2e / 1 Piece


Technical data sheet

Fastening clip 605, medium duty, G

Item number: 1018396



Dimensions



Length	75 mm
Width	14 mm
Height	37 mm
Dimension A	75 mm
Dimension B	61 mm
Dimension b	14 mm
Dimension D	40 mm
Dimension d	5.5 mm
Dimension e	7 mm
Dimension H	37 mm
Dimension t	1.5 mm

Technical data

Distance to the wall	no
Number of cables/pipes	1
Version for	Two-lobe
Fastening type	Screw hole
For diameter	40
Suitable in fire protection area	no
Halogen-free	yes
Plastic-covered	no
Hole size	5,5 x 7
Material thickness	1.5 mm
Nominal diameter	40 mm
UV-resistant	yes