

Technical data sheet

Profile rail, 17 mm slot, perforated, black

Item number: 1104293



Middle C profile rail for cable routing, in connection with clamp clips with hammer-head foot Can also be used as a suspended construction for cable tray systems.



- St** Steel
- P135** PES135 - Polyester

Master data		
Item number	1104293	
Type	CML3518P0400 SW	
Description 1	Profile rail	
Description 2	perforated, slot 17mm	
Manufacturer	OBO	
Dimension	400x35x18	
Colour	Jet black; RAL 9005	
Material	Steel	
Surface	PES135 - Polyester	
Surface standard		
Smallest sales unit	10	
Unit of quantity	Piece	
Weight	30 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,7256 kg CO2e / 1 Piece	

Item number: 1104293



Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value Iy	0.41 cm ⁴
Static value Iz	1.81 cm ⁴
Static value Wy	0.41 cm ³
Static value Wz	1.03 cm ³