

Technical data sheet

Profile rail, 17 mm slot, perforated, black

Item number: 1104307



Middle C profile rail for cable routing, in connection with clamp clips with hammer-head foot Can also be used as a suspended construction for cable tray systems.



St	Steel
P135	PES135 - Polyester

Master data

Item number	1104307
Type	CML3518P0500 SW
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	500x35x18
Colour	Jet black; RAL 9005
Material	Steel
Surface	PES135 - Polyester
Surface standard	
Smallest sales unit	10
Unit of quantity	Piece
Weight	37.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,904 kg CO2e / 1 Piece


Technical data sheet

Profile rail, 17 mm slot, perforated, black

Item number: 1104307



Dimensions



Length	500 mm
Width	35 mm
Height	18 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value I _y	0.41 cm ⁴
Static value I _z	1.81 cm ⁴
Static value W _y	0.41 cm ³
Static value W _z	1.03 cm ³