


Technical data sheet

CL2008 profile rail, slot 11 mm, perforated, breakable

Item number: 1105906



Light-duty C profile rail for cable routing, in conjunction with series clips or clamp clips with N foot. Can also be used in building of control cabinets.
Perforated, cannot be broken.



St	Steel
FS	Strip galvanised

Master data

Item number	1105906
Type	CL2008BP1000FS
Description 1	Profile rail
Description 2	perforated, slot 11mm
Manufacturer	OBO
Dimension	1000x20x8
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	10
Unit of quantity	Metre
Weight	21.5 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,5401 kg CO2e / 1 Meter


Technical data sheet

CL2008 profile rail, slot 11 mm, perforated, breakable

Item number: 1105906



Dimensions



Length	1,000 mm
Width	20 mm
Height	8 mm
Dimension L	1,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	10 mm
Bundle	10 m
Maintain electrical functions	no
Material thickness	0.75 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Slot width	11 mm
Static value A	0.24 cm ²
Static value I _y	0.02 cm ⁴
Static value I _z	0.17 cm ⁴
Static value W _y	0.05 cm ³
Static value W _z	0.17 cm ³