

Technical data sheet

CL2510 profile rail, slot 11 mm, BK, unperforated

Item number: 1107038



Light-duty C profile rail for cable routing, in conjunction with series clips or clamp clips with N foot. Can also be used in building of control cabinets. Unperforated, non-breakable.



St	Steel
BK	Bright

Master data

Item number	1107038
Type	CL2510UP2000BK
Description 1	Profile rail
Description 2	unperforated, slot 11mm
Manufacturer	OBO
Dimension	2000x25x10
Material	Steel
Surface	Bright
Surface standard	
Smallest sales unit	20
Unit of quantity	Metre
Weight	36 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,7267 kg CO2e / 1 Meter


Technical data sheet

CL2510 profile rail, slot 11 mm, BK, unperforated

Item number: 1107038



Dimensions



Length	2,000 mm
Width	25 mm
Height	10 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Without
Version for	Single profile
Bundle	50 m
Maintain electrical functions	no
Material thickness	1 mm
With perforation	no
With tothing	no
Profile shape	C profile
Slot width	11 mm
Static value A	0.52 cm ²
Static value I _y	0.08 cm ⁴
Static value I _z	0.44 cm ⁴
Static value W _y	0.13 cm ³
Static value W _z	0.35 cm ³