


Technical data sheet

AML3518 anchor rail, slot 16.5 mm, FT, unperforated

Item number: 1118153



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1118153
Type	AML3518UP6000FT
Description 1	Profile rail
Description 2	unperforated, slot 16.5mm
Manufacturer	OBO
Dimension	6000x35x18
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	6
Unit of quantity	Metre
Weight	94.84 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,9999 kg CO2e / 1 Meter


Technical data sheet

AML3518 anchor rail, slot 16.5 mm, FT, unperforated

Item number: 1118153



Dimensions



Length	6,000 mm
Width	35 mm
Height	18 mm
Dimension L	6,000 mm

Technical data

Breakable	no
Type of perforation	Without
Version for	Single profile
Bundle	6 m
Maintain electrical functions	no
Material thickness	1.5 mm
With perforation	no
With tothing	no
Profile shape	C profile
Slot width	16.5 mm
Static value A	1.14 cm ²
Static value I _y	0.49 cm ⁴
Static value I _z	0.85 cm ⁴
Static value W _y	0.44 cm ³
Static value W _z	1.05 cm ³