


Technical data sheet

AML3518P anchor rail, slot 16.5 mm, round-perforated FT

Item number: 1119826



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1119826
Type	AML3518P0200SOFT
Description 1	Profile rail
Description 2	perforated, slot 16.5mm
Manufacturer	OBO
Dimension	200x35x18
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	50
Unit of quantity	Piece
Weight	17.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4016 kg CO2e / 1 Piece


Technical data sheet

AML3518P anchor rail, slot 16.5 mm, round-perforated FT

Item number: 1119826



Dimensions



Length	200 mm
Width	35 mm
Height	18 mm
Dimension L	200 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Material thickness	1.5 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	16.5 mm
Static value A	0.96 cm ²
Static value I _y	0.49 cm ⁴
Static value I _z	1.85 cm ⁴
Static value W _y	0.44 cm ³
Static value W _z	1.05 cm ³