

Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, A2, perforated

Item number: 1121960



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



A2 Stainless steel

2B Bright, treated

Master data

Item number	1121960
Type	MS4022P2000A2
Description 1	Profile rail
Description 2	perforated, slot 18mm
Manufacturer	OBO
Dimension	2000x40x22,5
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	152.5 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,6047 kg CO2e / 1 Meter


Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, A2, perforated

Item number: 1121960



Dimensions



Length	2,000 mm
Width	40 mm
Height	22.5 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	no
Material thickness	2 mm
With perforation	yes
With toothing	no
Profile shape	C profile
ROHS-conformant	yes
Slot width	18 mm
Static value A	1.74 cm ²
Static value I _y	1.18 cm ⁴
Static value I _z	4.45 cm ⁴
Static value W _y	1.05 cm ³
Static value W _z	2.23 cm ³