

Technical data sheet

Junction box A 11 with terminal strip

Item number: 2000326



Protection rating IP55, rated voltage 690 V, nominal cross-section 2.5 mm², 12 entries for cable diameters of 5–14 mm.

Clamshell.

Dimensions: 85 x 85 x 40 mm

Clear internal dimensions: 75 x 75 x 35 mm

1 cut-out tool for every 10 boxes

A 11/5 VDE

1 terminal strip type 689



PE Polyethylene

Master data

Item number	2000326
Type	A 11 5
Description 1	Junction box
Description 2	with terminal strip
Manufacturer	OBO
Dimension	85x85x40
Colour	Light grey; RAL 7035
Material	Polyethylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	7.64 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1894 kg CO2e / 1 Piece


Technical data sheet

Junction box A 11 with terminal strip

Item number: 2000326



Dimensions



Length	85 mm
Width	85 mm
Height	40 mm

Technical data

Expandable	yes
No. of entries	12
Number of terminals	5
Type of entry	Cable
Type of entry	Cable
Type of housing penetration	Pre-marking
Measured insulation voltage V_i	690 V
Equipment	Terminal
Cover	Not transparent
Cover fastening	Locking
Entry from rear	no
Entries	12 entries for cable diameter 5–14 mm
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Square
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
for pipe diameter	14 mm
Halogen-free	yes
Clear internal dimensions	75x75x35 mm
Max. Conductor cross-section	2.5 mm ²
With screening	no
with lid	yes
Mounting in the earth	no
Mounting underwater	no
Mounting type	Wall/ceiling mounting
Nominal cross-section, min.	2.5 mm ²
Nominal voltage	690 V
Sealable	no
ROHS-conformant	yes
Protection rating	IP55
Permitted temperature range, max.	45 °C

Technical data sheet

Junction box A 11 with terminal strip

Item number: 2000326



Technical data

Permitted temperature range, min.	-5 °C
Transparent lid	no
Castable	no
Sealing compound supplied	no
Weatherproof	no
Junction box cover version	Blanking lid