

# Technical data sheet

## Junction box X 02 with terminal strip

Item number: 2005194



Junction box with terminal strip for the connection of cables and lines indoors and in outdoor areas. Square design with knock-out entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Including terminal strip, 5-pole.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK09 according to DIN EN 50102. Protection rating IP67 according to DIN EN 60529.

The scope of delivery contains a 5-pole terminal strip.



PC Polycarbonate

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 2005194                  |
| Type                               | X02 T LGR                |
| Description 1                      | Junction box             |
| Description 2                      | with terminal strip      |
| Manufacturer                       | OBO                      |
| Dimension                          | 95x95x72                 |
| Colour                             | Light grey; RAL 7035     |
| Material                           | Polycarbonate            |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 19.3 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,8278 kg CO2e / 1 Piece |


# Technical data sheet

## Junction box X 02 with terminal strip

Item number: 2005194



### Dimensions



|        |       |
|--------|-------|
| Length | 95 mm |
| Width  | 95 mm |
| Height | 72 mm |

### Technical data

|                                   |                                                           |
|-----------------------------------|-----------------------------------------------------------|
| Expandable                        | yes                                                       |
| No. of entries                    | 7                                                         |
| Type of entry                     | Cuttable stepped membrane                                 |
| Type of housing penetration       | Pre-marking                                               |
| Measured insulation voltage $V_i$ | 750 V                                                     |
| Equipment                         | Terminal                                                  |
| Cover                             | Not transparent                                           |
| Cover fastening                   | Screwed                                                   |
| Entry from rear                   | no                                                        |
| Entries                           | 7 x Ø20                                                   |
| Explosion-tested version          | no                                                        |
| Flame-resistant                   | acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C |
| Shape                             | Square                                                    |
| Fibre-glass reinforced            | yes                                                       |
| Halogen-free                      | yes                                                       |
| Clear internal dimensions         | 85x85x57 mm                                               |
| Max. Conductor cross-section      | 2.5 mm <sup>2</sup>                                       |
| With screening                    | no                                                        |
| with lid                          | yes                                                       |
| Mounting type                     | Wall/ceiling mounting                                     |
| Nominal cross-section, max.       | 2.5 mm <sup>2</sup>                                       |
| Nominal cross-section, min.       | 1 mm <sup>2</sup>                                         |
| Nominal voltage                   | 750 V                                                     |
| Sealable                          | yes                                                       |
| Impact-resistant                  | yes                                                       |

# Technical data sheet

## Junction box X 02 with terminal strip

Item number: 2005194



### Technical data

|                                   |        |
|-----------------------------------|--------|
| Protection rating                 | IP67   |
| Protection rating IK code         | IK09   |
| Permitted temperature range, max. | 65 °C  |
| Permitted temperature range, min. | -25 °C |
| Transparent lid                   | no     |
| Weatherproof                      | yes    |