

Technical data sheet

Junction box T 100, closed, OBO EcoLine

Item number: 2007257



Junction box for the connection of cables indoors and in protected outdoor areas. Rectangular design without entries. Suitable for wall and ceiling mounting and on mounting panels. With the option of fastening inside and to mount via the corner domes. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK07 according to DIN EN 50102



Master data

Item number	2007257
Type	T 100 OE ECO
Description 1	Junction Box
Description 2	without entries
Available from	08.03.2026
Manufacturer	OBO
Dimension	150x116x67
Colour	Light grey; RAL 7035
Material	Polypropylene Eco
Smallest sales unit	1
Unit of quantity	Piece
Weight	16.35 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3649 kg CO2e / 1 Piece


Technical data sheet

Junction box T 100, closed, OBO EcoLine


Item number: 2007257



Dimensions



Length	150 mm
Width	116 mm
Height	67 mm



Technical data

Expandable	yes
Type of entry	None
Type of entry	Cable
Type of housing penetration	Without
Measured insulation voltage V_i	500 V
Equipment	Without
Cover	Not transparent
Cover fastening	Screwed
Entry from rear	yes
Entries	None
Explosion-tested version	no
Flame-resistant	Acc. to VDE 0471/DIN 695 Part 2-1, test temperature 750°C
Shape	Rectangular
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Halogen-free	yes
Clear internal dimensions	136x102x57 mm
With screening	no
with lid	yes
Mounting type	Wall/ceiling mounting
Nominal cross-section, min.	10 mm ²
Nominal voltage	500 V
Sealable	yes
Protection rating	IP66
Protection rating IK code	IK07.
Permitted temperature range, max.	65 °C
Permitted temperature range, min.	-25 °C

Technical data sheet

Junction box T 100, closed, OBO EcoLine

Item number: 2007257



Technical data

Transparent lid	no
Weatherproof	no
Junction box cover version	Blanking lid