


# Technical data sheet

## Junction box T 60, plug-in seal, terminal strip

Item number: 2007434



Junction box with terminal strip for the connection of cables and lines indoors and in protected outdoor areas. Square design with plug-in seals to the sides and knock-out entries in the bottom. Suitable for wall and ceiling mounting and on mounting panels. With the option to fasten inside and to mount via the corner domes. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK07 according to DIN EN 50102.



**PP** Polypropylene

### Master data

|                                    |                               |
|------------------------------------|-------------------------------|
| Item number                        | 2007434                       |
| Type                               | T 60 KL                       |
| Description 1                      | Junction box                  |
| Description 2                      | with terminal strip + entries |
| Manufacturer                       | OBO                           |
| Dimension                          | 114x114x57                    |
| Colour                             | Light grey; RAL 7035          |
| Material                           | Polypropylene                 |
| Smallest sales unit                | 5                             |
| Unit of quantity                   | Piece                         |
| Weight                             | 16.7 kg                       |
| Weight unit                        | kg/100 pc.                    |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,6287 kg CO2e / 1 Piece      |


# Technical data sheet

## Junction box T 60, plug-in seal, terminal strip

Item number: 2007434



### Dimensions



|        |        |
|--------|--------|
| Length | 114 mm |
| Width  | 114 mm |
| Height | 57 mm  |

### Technical data

|                                   |                                                           |
|-----------------------------------|-----------------------------------------------------------|
| Expandable                        | yes                                                       |
| No. of entries                    | 7                                                         |
| Number of terminals               | 5                                                         |
| Type of entry                     | Plug-in seal                                              |
| Type of entry                     | Cable                                                     |
| Type of housing penetration       | Cuttable stepped membrane                                 |
| Measured insulation voltage $V_i$ | 500 V                                                     |
| Equipment                         | Terminal                                                  |
| Cover                             | Not transparent                                           |
| Cover fastening                   | Screwed                                                   |
| Entry from rear                   | yes                                                       |
| Entries                           | 7 x M25                                                   |
| Explosion-tested version          | no                                                        |
| Flame-resistant                   | acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C |
| Shape                             | Square                                                    |
| Maintain electrical functions     | Without                                                   |
| For Ex zone                       | Without                                                   |
| For Ex zone gas                   | Without                                                   |
| For Ex zone dust                  | Without                                                   |
| Fibre-glass reinforced            | no                                                        |
| Halogen-free                      | yes                                                       |
| Clear internal dimensions         | 100x100x48 mm                                             |
| With screening                    | no                                                        |
| with lid                          | yes                                                       |
| Mounting type                     | Wall/ceiling mounting                                     |
| Nominal cross-section, min.       | 6 mm <sup>2</sup>                                         |
| Nominal voltage                   | 500 V                                                     |
| Sealable                          | yes                                                       |
| ROHS-conformant                   | yes                                                       |

# Technical data sheet

Junction box T 60, plug-in seal, terminal strip

Item number: 2007434



## Technical data

|                                   |       |
|-----------------------------------|-------|
| Protection rating                 | IP66  |
| Protection rating IK code         | IK07. |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |
| Transparent lid                   | no    |
| Weatherproof                      | no    |