

Technical data sheet

Dolü branch terminals, open on both sides, 10-pole

Item number: 2055503



Terminals made of brass, screws of steel, galvanised and transparently passivated, 10-pole, strip separable into individual terminals, open on both sides. Captive upwards screw.
Nominal cross-section $10 \pm \text{mm}^2$.
Nominal voltage 380 V.
Max. connectable cross-sections per terminal: $3 \times 10 \text{ mm}^2$, $4 \times 6 \text{ mm}^2$.



PP Polypropylene

Master data

Item number	2055503
Type	71
Description 1	Dolü branch terminal
Manufacturer	OBO
Dimension	10 mm^2
Colour	Black
Material	Polypropylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	7.03 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1866 kg CO2e / 1 Piece


Technical data sheet

Dolü branch terminals, open on both sides, 10-pole

Item number: 2055503



Dimensions



Length	146.7 mm
Width	17 mm
Height	24.8 mm

Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, max.	10 mm ²
Connectable conductor cross-section, single-wire, min.	6 mm ²
Connection position	Side
No. of terminals	10
Number of screwless terminals per pole	1
Version of electrical connection 1	Screw connection
Drill hole spacing, centre	14.8 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	no
Suitable for multi-wire conductors	yes
Insulation material	Thermoplast
Mounting type	Direct mounting
Nominal cross-section, min.	10 mm ²
Nominal voltage	380 V
Nominal current	24 A
Pole number	10
Cross-section	Max. connectable cross-sections per terminal: 3 x 10 mm ² , 4 x 6 mm ² mm ²
Transparent	no