

Technical data sheet

Collecting clamp Grip 70, metal A4

Item number: 2207164



Metal grouped support for high mechanical stability, even in case of fire. Suitable for safe mounting above fire protection ceilings. Also approved as a cable-specific variant for the maintenance of electrical function to DIN 4102 Part 12. For wall and ceiling mounting. Lock can be opened without tools. Detailed information on the approved routing variants can be found in the appropriate testing documentation.



A4	Stainless steel
2B	Bright, treated

Master data

Item number	2207164
Type	2031 M 70 A4
Description 1	Grip collecting clamp
Manufacturer	OBO
Dimension	70x NYM3x1,5
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	10
Unit of quantity	Piece
Weight	37 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0126 kg CO2e / 1 Piece


Technical data sheet

Collecting clamp Grip 70, metal A4

Item number: 2207164



Dimensions



Technical data

No. of conductors NYM 3 x 1.5	70
Maintain electrical functions	yes
Halogen-free	yes
With anchor	no
ROHS-conformant	yes