

Technical data sheet

Tilting anchor

Item number: 3482707



Including nut and large washer.

The universal heavy-duty fastening for stressed concrete, hollow steel profiles, metal sheets and plates.

Use: heating, ventilation and air conditioning technology, cooling systems, sprinkler systems, pipes, cable tracks, etc.

* Dependent on the thickness of the ceiling profile.



St

Steel

G

Electrogalvanised

Master data

Item number	3482707
Type	KD 8 100
Description 1	Tilting anchors
Manufacturer	OBO
Dimension	M8x100mm
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	25
Unit of quantity	Piece
Weight	11.2 kg
Weight unit	kg/100 pc.

Dimensions

Length	100 mm
Dimension L	100 mm

Technical data sheet

Tilting anchor

Item number: 3482707



Technical data

Version for	With threaded shaft
Drill hole	22 mm
Drill hole diameter, min.	22 mm
Breaking load	2.4 kN
Thread	M8
Thread type	Metric
Minimum cavity depth	75 mm
With washer	yes
Protection ring for ceramics	no