

Technical data sheet

Porous concrete anchor with M10 external thread

Item number: 3497616



Steel spreading anchor tested for fire protection properties and approved for use in porous concrete.

Version with external thread. Suitable for fire loads of up to 120 minutes, please refer to the general construction approval for the load values (applies to porous concrete of resistance classes of min. 3.3).

A setting tool is required for mounting.



DIBt U

St Steel

G Electrogalvanised

Master data

Item number	3497616
Type	PBD M10x10
Description 1	Aerated concrete anchor
Description 2	with external thread
Manufacturer	OBO
Dimension	90x14
Colour	zinc
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	25
Unit of quantity	Piece
Weight	11.4 kg
Weight unit	kg/100 pc.


Technical data sheet

Porous concrete anchor with M10 external thread

Item number: 3497616



Dimensions



Length	90 mm
Dimension L	90 mm

Technical data

Version for	For knocking in
Thread	M10
Thread metric	10
Thread type	Metric
Clamping strength	10 mm
ROHS-conformant	yes