

Technical data sheet

Round conductor, stainless steel A4

Item number: 5021642



- Can be used as an earthing conductor according to DIN EN 62561-2 (VDE 0185-561-2)
- Corresponds to the requirements of VDE 0185-305 (IEC 62305)
- RD 10-V4A for applications in the earth
- According to the foundation earth electrode standard DIN 18014, V4A is required in the earth



A4 Stainless steel

Master data

Item number	5021642
Type	RD 10-V4A
Description 1	Round conductors
Description 2	50 m ring
Manufacturer	OBO
Dimension	10mm
Material	Stainless steel 1.4571/1.4404
Smallest sales unit	50
Unit of quantity	Metre
Weight	63 kg
Weight unit	kg/100 m


Technical data sheet

Round conductor, stainless steel A4

Item number: 5021642



Dimensions



Dimension D	10 mm
-------------	-------

Technical data

Number of individual wires	1
High voltage-resistant, insulated version	no
Nomal ring (approx. kg)	32
Nomal ring (approx. m)	50
Length tolerance $\pm$	5 %
Cross-section	78 mm ²
Material property	Miscellaneous
Material jacket	Without