


Technical data sheet

Spacer for flat conductor, with polyamide base

Item number: 5033039



- Fit: FL 30
- With mounting hole 6.2 x 22 mm
- With 2 cylinder bolts M6 x 16 and over-piece from hot-dip galvanised steel
- Bottom section from polyamide, black



St

Steel

FT

Hot-dip galvanised

Master data

Item number	5033039
Type	833 35
Description 1	Spacer
Description 2	for steel strip
Manufacturer	OBO
Dimension	35mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	25
Unit of quantity	Piece
Weight	3.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1183 kg CO2e / 1 Piece


Technical data sheet

Spacer for flat conductor, with polyamide base

Item number: 5033039



Dimensions



Dimension B	60 mm
-------------	-------

Technical data

Fit	max. FL30 mm
ROHS-conformant	yes
Intermediate plate	no